AUM 011.E - washbasin, middle-size sink, with electric through-flow water heater - 230V, 50Hz



AUM 011 is the stainless steel, sensor-controlled, wall-mounted washbasin. The basin is equipped with a stainless steel facing, aerator and sensor. Water turns on automatically when the user's hands are placed within the sensor's range and turns off when they have been removed. Water stops running with a certain time delay after the hands have been removed from the scanning zone. The washbasin is equipped with the mechanism against excess pressure of hot and cold water. AUM 011 is manufactured from the stainless steel AISI 304. Other materials (e.g. AISI 316) possible on order. For cleaning we recommned WÜRTH detergents ? material preservation (no. 0893 121 K) and material cleaning (no. 893 121 1).

Rating: Not Rated Yet

Ask a question about this product

Manufacturer: AZP Brno

Description AUM 011 is the stainless steel, sensor-controlled, wall-mounted washbasin. The basin is equipped with a stainless steel facing, aerator and sensor. Water turns on automatically when the user's hands are placed within the sensor's range and turns off when they have been removed. Water stops running with a certain time delay after the hands have been removed from the scanning zone. The washbasin is equipped with the mechanism against excess pressure of hot and cold water. AUM 011 is manufactured from the stainless steel AISI 304. Other materials (e.g. AISI 316) possible on order. For cleaning we recommned WÜRTH detergents? material preservation (no. 0893 121 K) and material cleaning (no. 893 121 1).

Complete delivery

- 1. Sink with sheathing
- 2 Aerator
- 3. Electronics with the sensor
- 4. Electromagnetic valve
- 5. Corner valve with filter (AUM 011.2, .TV ? 2 pcs)
- 6. Spherical valve (AUM 011.2 TV)
- 7. Mixing valve (AUM 011.2)
- 8. Thermostatic valve (AUM 011.TV)
- 9. Through flow water heater (AUM 011.E)
- 10. Source of power supply ZAC E ? 12 V, 50 Hz (AUM 011.E)
- 11. Waste siphon
- 12. Connecting hoses
- 13. Cantilever
- 14. Fittings

Requirements for setting up the construction

- 1. The water supply set up? see the picture
- 2. The outlet set up on D= 40 mm

- 3. The power-supply cable is fixed for powering 12 V, 50 Hz from power-supply source ZAC (not applicable for AUM 011.E)
- 4. The power-supply cable CYKY 32C x 1,5 ? 2,5 for AUM 011.E is wired

Download information about the product

- AUM 011.1 data for projectants (98 kB)
- AUM 011.1B data for projectants (98 kB)
- AUM 011.2 data for projectants (98 kB)
- AUM 011.2B data for projectants (98 kB)
- AUM 011.E data for projectants (98 kB)
- AUM 011.TV data for projectants (98 kB)
- AUM 011.TVB data for projectants (98 kB)

Basic technical informationSensor radius

Water inlet

Outlet

Inner basin dimension

Adjustable after-action delay time

AUM 011.1, .2, .TV Water pressure

Electric powering

Input

Powering source

Electricity protection

Weight AUM 011.E

Recommended pressure

Power supply

self-adjusting G1/2" D=40 mm

370 x 240 x 150 mm 0 ? 4 s (set on 1 sec)

0,2 ? 0,6 MPa

12V, 50 Hz, or for battery versions 6V (4 x AA battery)

3 500 W

ZAC 1/20 (max. 3 x AUM 011)

IP 54 12,5 kg

0,3 MPa (without variances and air bubbles)

230 V, 50 Hz

Figures

