

AUM 015.TVB - round washbasin, wall mounted, with thermostatic valve - 6V (4x1,5)



AUM 015 is an automatic stainless wash basin to be fixed on wall. The wash basin is not equipped by usual sensor mixer but a durable st. steel arm is used with incorporated contactless sensor control. This way the wash basin is much more resistant to damage. Optoelectronic sensor reacts to hands under the arm ? when hands are placed to sensor zone water automatically starts running as the electromagnetic valve opens. The valve stays open for a pre-set period of time after hands are removed (decay time). Wash basin is equipped against hot water overpressure. Wash basin outlet is equipped by a stainless grid that prevents subjects from falling to waste trap. 6/4" nipple is welded to it to connect the waste trap or to allow direct discharge to sewerage drains (braz is assembled at another place). The wash basin has no welded-in moulding but is all welded from 1.5 mm thick metal sheet ? therefore it is much more resistant. Inner edges are welded at 90°. We also supply the wash basin as a bowl without arm. When ordering it needs to be specify if a wall mixer (without a hole in wash basin) or pillar mixer (diameter of hole in the wash basin on the left or on the right) is to be used. Outlet and fittings comprise a part of the delivery. The AUM 015 stainless steel washbasin, in its construction and finish, meets EU standards and is mainly intended for food processing industry. It may be utilized in any other operations, where increased hygienic standards along with maximal water savings are required AUM 015 is manufactured from the stainless steel AISI 304. Other materials (e.g. AISI 316) possible on order. For cleaning we recommned WÜRTH detergents ? material preservation (no. 0893 121 K) and material cleaning (no. 893 121 1).

Rating: Not Rated Yet

[Ask a question about this product](#)

Manufacturer: [AZP Brno](#)

Description AUM 015 is an automatic stainless wash basin to be fixed on wall. The wash basin is not equipped by usual sensor mixer but a durable st. steel arm is used with incorporated contactless sensor control. This way the wash basin is much more resistant to damage. Optoelectronic sensor reacts to hands under the arm ? when hands are placed to sensor zone water automatically starts running as the electromagnetic valve opens. The valve stays open for a pre-set period of time after hands are removed (decay time). Wash basin is equipped against hot water overpressure. Wash basin outlet is equipped by a stainless grid that prevents subjects from falling to waste trap. 6/4" nipple is welded to it to connect the waste trap or to allow direct discharge to sewerage drains (braz is assembled at another place). The wash basin has no welded-in moulding but is all welded from 1.5 mm thick metal sheet ? therefore it is much more resistant. Inner edges are welded at 90°. We also supply the wash basin as a bowl without arm. When ordering it needs to be specify if a wall mixer (without a hole in wash basin) or pillar mixer (diameter of hole in the wash basin on the left or on the right) is to be used. Outlet and fittings comprise a part of the delivery. The AUM 015 stainless steel washbasin, in its construction and finish, meets EU standards and is mainly intended for food processing industry. It may be utilized in any other operations, where increased hygienic standards along with maximal water savings are required AUM 015 is manufactured from the stainless steel AISI 304. Other materials (e.g. AISI 316) possible on order. For cleaning we recommned WÜRTH detergents ? material preservation (no. 0893 121 K) and material cleaning (no. 893 121 1). Complete delivery

1. sink with sheathing
2. automatic tap according to chosen type of power supply and water connection
3. connecting hoses
4. small assembly materials
5. waste siphon
6. 4x AA battery (for versions with battery supply)
7. through-flow water heater (for AUM 015.E)

Requirements for setting up the construction

- 1. Set-up water inlet as per picture
- 2. Set-up outlet d = 40 mm
- 3. Set-up cable for power supply ? 12 V, 50 Hz from source of power supply ZAC
- 4. For AUM 015.E set up supply cable CYKY 3C 1,5÷2,5

Download information about the product

- [AUM 015 data for projectants - \(29 kB \)](#)

Basic technical informationRadius of sensor

- Water inlet
- Water outlet
- Inner dimensions of sink
- Adjustable time of water flow
- AUM 015.1, .2, .TV (+ battery version)
- Water pressure
- Power supply
- Power requirement
- Source of power supply
- IP protection
- Weight
- AUM 015.E
- Recommended water pressure
- Power input

- self-adjusting
- ZAC 1/50 (max. 8x AUM 015.1,015.TV, 015.2)
- G 1/2?
- d = 40 mm
- d = 370 x 120 mm
- 0?4 s (adjusted to 1 s)
- 0,2?0,6 MPa
- 230 V, 50 Hz
- 6 VA
- ZAC 1/20 (max. 3x AUM 015.1, 015.TV, 015.2)
- IP 54
- 15,5 kg
- 0,3 MPa (without fluctuation and air bubbles)
- 3 500 W

Figures

