

TRM - stainless steel turnstiles



TRM 01, TRM 02 are stainless steel turnstiles intended for the through pass regulation of individuals. The turnstiles are one-way in right or left versions. TRM 01 is intended for connection to hand disinfectant ADR 01.3 and after pressing a button enables also a back stroke. The back stroke can be conditioned by using another device, e.g. a washing system for shoes. This variant needs to be specified when ordering. The TRM 02 works in a separate mode without the possibility of back stroke and does not require an electricity supply. The turning direction needs to be specified when ordering. The devices are intended to be wall mounted or in combination with a STR 01 column for installation on the floor.

Rating: Not Rated Yet
[Ask a question about this product](#)

Manufacturer: [AZP Brno](#)

Description TRM 01, TRM 02 are stainless steel turnstiles intended for the through pass regulation of individuals. The turnstiles are one-way in right or left versions. TRM 01 is intended for connection to hand disinfectant ADR 01.3 and after pressing a button enables also a back stroke. The back stroke can be conditioned by using another device, e.g. a washing system for shoes. This variant needs to be specified when ordering. The TRM 02 works in a separate mode without the possibility of back stroke and does not require an electricity supply. The turning direction needs to be specified when ordering. The devices are intended to be wall mounted or in combination with a STR 01 column for installation on the floor.

Complete delivery

- 1. device body
- 2. turning arms
- 3. driving unit (only TRM 01)
- 4. blocking unit (only TRM 02)

Requirements for setting up the construction

- 1. Setup cable for power supply ? 12 V, 50 Hz from source of power supply ZAC (only TRM 01)

Basic technical informationTRM 01

Electricity protection	IP 55
Power supply	12 V, 50 Hz
Power requirement	24 VA
Source of power supply	ZAC 1/50 (max. 2 x TRM 01)
Dimensions (l x w x h)	350 x 350 x 1 050 mm
Device capacity	20 individuals per minute
Weight	8 kg
TRM 02	
STR 01	

Figures

